

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

M49 X 0.75 Mounted UV/IR Cut-Off Filter



Stock #54-749 3-4 DAYS



1



€210,00

ADD TO CART

Qty 1-9

€210,00

Qty 10+

€192,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
46.8

Filter Thread:
M49 x0.75

Cut-Off Wavelength (nm):
690.00

Cut-On Wavelength (nm):

390.00
Index of Refraction n_d: 1.52 Substrate, Varies by Layer
Note: AR Coating: Both Surfaces Multi-Layer
Outer Diameter (mm): 51.0
Substrate: ☐ Float Glass
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 7.0
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant