

M58 x 0.75 Mounted IR Cut-Off Filter



Stock **#54-747** CLEARANCE ☐ In Stock

-

1

+

€85,95

ADD TO CART

Qty 1+

€85,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
52.8

Filter Thread:
M58 x 0.75

Cut-Off Wavelength (nm):
750.00

Glass/Filter Number:
[SCHOTT KG3](#)

Index of Refraction n_d :
1.52

Note: AR Coating: Both Surfaces Multilayer Broadband AR
Outer Diameter (mm): 60.0
Substrate: Schott KG-3
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 7.0
Type: Mounted Imaging Filter
Wavelength Range (µm): 0.3 - 2.7
Wavelength Range (nm): 300 - 2700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant