

M58 x 0.75 Variable Neutral Density (ND) Filters



Variable Neutral Density (ND) Machine Vision Filter

Stock **#16-079** 3-4 DAYS



1



€153,00

ADD TO CART

Qty 1-9

€153,00

Qty 10+

€141,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.5 - 4.0 @ 550 - 650nm

Clear Aperture CA (mm):
53.5

Filter Thread:
M58 x0.75

Substrate:  Polymer Film XP42
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Clear Aperture (%): 53.5
Mount Thickness (mm): 5.85
Note: AR Coated
Coating Specification: R_{avg} ≤2% @ 400 - 700nm
Mount Diameter (mm): 60.3 ±0.2
Mount Thickness Including Threads (mm): 7.85

Regulatory Compliance

Certificate of Conformance: View
--