

M6 x 1.0 Bumper (Package of 4), Sorbothane Bumpers



Stock #56-923 ☐ In Stock

-

1

+

€44⁵⁰

ADD TO CART

Qty 1-2
€44,50
Qty 3+
€39,40
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Metric	Type:
Thread Type: M6	Note:
Physical & Mechanical Properties	
25.40	Thickness (mm):
Sorbothane	Construction:
38.10	Diameter (mm):
30-65 / bumper	Load Capacity (lbs):
Threading & Mounting	
12.7	Thread Length (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 211:
View	Certificate of Conformance:

PRODUCT DETAILS

- Absorb and Dissipate Vibration
 - Stabilize Equipment up to 152lbs
 - English, Metric, or Universal Styles
- Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.