

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

M62 X 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #36-444 CLEARANCE 3-4 DAYS



1



€21,95

ADD TO CART

Qty 1+

€21,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
58.00

Coating:  
Uncoated

Diameter (mm):  
64.50

Extinction Ratio:  
Approx. 19:1 at 400nm  
Approx. 200:1 at 500nm  
≥2700:1 at 550-650nm

|                                                           |
|-----------------------------------------------------------|
| Approx. 600:1 at 700nm                                    |
| <b>Filter Thread:</b><br>M62 x0.75                        |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Operating Temperature (°C):</b><br>-15 to +70          |
| <b>Polarization:</b><br>95% Efficiency                    |
| <b>Transmission (%):</b><br>Single: 30<br>Crossed: 0.15   |
| <b>Type:</b><br>Mounted Imaging Filter                    |
| <b>Construction:</b><br>Dichroic                          |
| <b>Mount Thickness (mm):</b><br>9                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                |
| <b>Mount Thickness Including Threads (mm):</b><br>11      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |