

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

M67 X 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #64-900 ■ In Stock



1



€62,00

ADD TO CART

Qty 1-9

€62,00

Qty 10+

€58,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
62.00

Coating:
Uncoated

Diameter (mm):
70.00 +0/-0.2

Extinction Ratio: Approx. 19:1 at 400nm Approx. 200:1 at 500nm ≥2700:1 at 550-650nm Approx. 600:1 at 700nm
Filter Thread: M67 x0.75
Substrate: ☐ Float Glass
Operating Temperature (°C): -15 to +70
Polarization: 95% Efficiency
Transmission (%): Single: 30 Crossed: 0.15
Type: Mounted Imaging Filter
Construction: Dichroic
Mount Thickness (mm): 9 ±0.1
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 11

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View