

TECHSPEC[®] Machine Vision Filter Kit - M30.5 x 0.5 Filter Thread



High Performance Mounted Machine Vision Filter Kit

Stock #11-030 3-4 DAYS

-

1

+

€1.495⁰⁰

ADD TO CART

Qty 1-9

€1.495,00

Qty 10+

€1.371,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Number of Filters:

Filters Included :
[NUV](#), [Blue](#), [Cyan](#), [Green](#), [UV/IR Cut-Off](#), [Orange](#),
[Light Red](#), [Dark Red](#), [UV/VIS Cut-Off](#)

Physical & Mechanical Properties

32.50 Diameter (mm):

Threading & Mounting

M30.5 x0.50 Filter Thread:

Regulatory Compliance

[Compliant](#) RoHS:

[View](#) Certificate of Conformance:

PRODUCT DETAILS

- 9 Machine Vision Filters with M25.5 or M30.5 Threading
- Center Wavelengths from 330nm to 880nm
- High Transmission Up to 96%
- Individual [Machine Vision Filters](#) also Available
- Note: Potential change of packaging

TECHSPEC® High Performance Mounted Machine Vision Filter Kits include all nine [TECHSPEC High Performance Mounted Machine Vision Filter](#) options with wavelengths spanning the UV, Visible, and NIR spectra. The included filters are designed for use with common LED wavelengths and provide superior blocking compared to traditional filters. These filter kits are available in two versions: one with M25.5 threaded filters and the other with M30.5 threaded filters. TECHSPEC High Performance Machine Vision Filter Kits are ideal for prototyping machine vision applications to determine which filter most improves image contrast. Individual [mounted machine vision filters](#) in additional thread sizes from M22.5 to M62.0 are also available.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.