

[See all 13 Products in Family](#)

TECHSPEC[®]

C-Mount, 35mm Sq. x 1mm Thick Plate Mount



Stock **#56-264** 3 In Stock

-

1

+

€292^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€292,00 each
Qty 5-9	€257,70 each
Qty 10-25	€237,20 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Function:

Optic Mount (Fixed)

Type of Optics:

Square

Note:

Includes one C-Mount Aperture Cap [\(#55-245\)](#)

Dimensions of Compatible Optics (mm):

35.0 Sq.

Physical & Mechanical Properties

38.0 x 38.0 x 50.0
Dimensions (mm):

38.0
Extension Length (mm):

1.0
Min. Thickness of Compatible Optics (mm):

1.0
Max. Thickness of Compatible Optics (mm):

Threading & Mounting

C-Mount
Thread Type:

1/4-20
Compatible Post:

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

