

Mounted M30.5 x 0.5 Threaded - Red Filter



Stock **#46-545** ☒ In Stock

-

1

+

€53,50

ADD TO CART

Qty 1-9
€53,50
Qty 10+
€49,40
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
27.0

Filter Thread:
M30.5 x0.50

Color:
Red

Cut-On Wavelength (nm):

600.00
Glass/Filter Number: R-60
Index of Refraction n_d: 1.53
Note: AR Coating: MgF ₂
Outer Diameter (mm): 32.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View