

## Mounted M46 x 0.75 Threaded - Green Filter



Stock #54-768 □ In Stock

⊖ 1 ⊕ **€56,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €56,50                        |
| Qty 10+                       |
| €52,50                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
41.5

Filter Thread:  
M46 x0.75

Color:  
Green

Cut-Off Wavelength (nm):

|                                                             |
|-------------------------------------------------------------|
| 550.00                                                      |
| <b>Cut-On Wavelength (nm):</b><br>520.00                    |
| <b>Glass/Filter Number:</b><br>G-533                        |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.54        |
| <b>Mount Thickness (mm):</b><br>4.4 ±0.1                    |
| <b>Mount Thickness Including Threads (mm):</b><br>6.4       |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                |
| <b>Outer Diameter (mm):</b><br>48.0                         |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Substrate Thickness (mm):</b><br>2.5                     |
| <b>Surface Quality:</b><br>80-50                            |
| <b>Thickness of Compatible Optics (mm):</b><br>2.5          |
| <b>Thickness with Mount (mm):</b><br>5.00                   |
| <b>Type:</b><br>Mounted Imaging Filter                      |
| <b>Type of Filter:</b><br>Hoya G-533 or equivalent          |
| <b>Wavelength Range (nm):</b><br>400 - 700                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |