

[See all 17 Products in Family](#)

Mounted M58 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock **#54-046** 1 In Stock

-

 1

+

 €71⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€71,00 each
Qty 10-25	€64,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounted Imaging Filter

Type:

Physical & Mechanical Properties

53.0

Clear Aperture CA (mm):

60.0

Outer Diameter (mm):

4.50	Thickness with Mount (mm):
2.00 ±0.2	Thickness (mm):

Optical Properties

390.00	Cut-On Wavelength (nm):
L-39	Glass/Filter Number:

Hoya L-39	Substrate: ☐
AR Coated	Coating:

Clear	Color:
80-50	Surface Quality:

R _{avg} >2% @ 400 - 700nm	Coating Specification:
350 - 2200	Wavelength Range (nm):

4 - 6λ	Surface Flatness (P-V):
--------	-------------------------

Threading & Mounting

M58 x0.75	Filter Thread:
-----------	----------------

Environmental & Durability Factors

-15 to +70	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information

