

Mounted M67 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock **#46-578** 3-4 DAYS

⊖ 1 ⊕ **€60,00**

ADD TO CART

Qty 1-9
€60,00
Qty 10+
€56,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
62.0

Cut-On Wavelength (nm):
350.00

Filter Thread:
M67 x0.75

Glass/Filter Number: Optical Glass
Substrate: □ Optical Glass
Operating Temperature (°C): -15 to +70
Coating: Multi-coated
Color: Clear
Outer Diameter (mm): 69.0 +0/-0.2
Thickness with Mount (mm): 5.50
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1
Type: Mounted Imaging Filter
Coating Specification: R _{avg} >2% @ 500 - 700nm
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View