

[See all 4 Products in Family](#)

## Multi-Grid Standard Stage Micrometer w/ NIST Cert



Stock **#59-275** **1 In Stock**

- 1 + €955<sup>.00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€955,00 each
Qty 5+	€907,60 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**NIST Certification:**

Yes

### Physical & Mechanical Properties

**Scale Divisions:**

0.5mm (25µm divisions), 1.0mm (50µm divisions),  
2.0mm (100µm divisions), 4.0mm (200µm  
divisions), angle grid (15° segments)

**Dimensions (mm):**

25.4 x 76.2

1.50 ±0.100 **Thickness (mm):**

±0.100 **Dimensional Tolerance (mm):**

## Optical Properties

Chrome on Glass **Substrate:**

60-40 **Surface Quality:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

## Product Details

- Calibrate Distortion in High Magnification Systems

The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Micrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.