

# Nikon 200mm Large FOV Tube Lens

See More by [Nikon](#)



Stock #75-379 **NEW** 1 In Stock

⊖ 1 ⊕ €1.340<sup>00</sup>

**ADD TO CART**

## Volume Pricing

Qty 1+	€1.340,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Type:  
Tube Lens

Manufacturer:  
Nikon

### Physical & Mechanical Properties

Length (mm):  
27.00

Maximum Diameter (mm):

### Optical Properties

200.00 Focal Length FL (mm):

1x Magnification:

380 - 1000 Wavelength Range (nm):

25 Field Number (mm):

42 Entrance Pupil Diameter (mm):

### Threading & Mounting

M43x0.5 Mounting Threads:

### Regulatory Compliance

[View](#) Certificate of Conformance:

## Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

## Technical Information

Dimensions (mm)						
Stock No.	Magnification	Parfocal Length	A	B	C	D
#75-345	4X	60.06	30.0	44.3	19.7	M25 x 0.75
#88-375	10X	60.06	32.0	58.9	12.0	M25 x 0.75
#88-376	20X	59.90	33.5	58.9	9.0	M25 x 0.75
#75-346	40X	60.06	32.0	59.8	8.3	M25 x 0.75

