

[See all 2 Products in Family](#)

# Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 30cc

See More by [Norland](#)



Norland Index Matching Liquid (IML) 150 Preloaded Syringe, 30cc

Stock **#17-408** **7 In Stock**

⊖ 1 ⊕ €60.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€60,00 each
Qty 5-11	€54,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

1	Size (oz):
IML 150	Norland Number:
8 months	Shelf Life:
	Type:

Barrel

**Note:**

Requires [30cc Hand Plunger](#) or [30cc DispensGun](#) and [Dispensing Tips](#) for use

## Optical Properties

**Index of Refraction ( $n_d$ ):**

1.52

## Material Properties

**Viscosity (cps):**

100

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 253:**

[Compliant](#)

## Product Details

- 1.52 Index of Refraction at 589nm
- Ideal for Temporary Fiber Slicing
- 6g or 30g Preloaded Syringes

Norland Index Matching Liquid (IML) 150 is a low viscosity liquid monomer used as an index matching media for temporary fiber slicing. Unlike silicone index matching liquids which are difficult to completely remove from a fiber end after use, IML 150 is easily removed using acetone. This index matching liquid can also be used between two optical elements to eliminate reflection losses caused by glass-air interfaces. Norland Index Matching Liquid (IML) 150 is available in preloaded syringes with either 6g or 30g of liquid. IML 150 does not cure and will always remain a liquid.