

NUV M25.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-740 3-4 DAYS

⊖ 1 ⊕ **€124,00**

ADD TO CART

Qty 1-9
€124,00
Qty 10+
€117,70
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-250, 400-670

Clear Aperture CA (mm):
21.00

Coating:
Hard Coated

Filter Thread: M25.5 x0.50
Color: NUV
Center Wavelength CWL (nm): 324.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 105.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 27.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
