

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Hoya O56 (560nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-089 3-4 DAYS



1



€88,00

ADD TO CART

Qty 1-10

€88,00

Qty 11+

€78,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
560±6

Cut-On Wavelength (nm):
560.00 ±6

Density (g/cm³): 2.68
Glass/Filter Number: Hoya Q56
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Orange
Surface Quality: 80-50
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: VS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View