

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

OD 3.0 NIR, 25mm Dia. Non-Reflective ND Filter



Non-Reflective Neutral Density (ND) Filters

Stock #63-415 3-4 DAYS



1



€141,00

ADD TO CART

Qty 1-10

€141,00

Qty 11+

€126,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.10

Optical Density OD (Average):
3.0

Substrate:
[B270](#)

Coating: Non-Reflective ND
Reflection (%): ≤1.5
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.1
Transmission (%): 0.10
Transmission Tolerance (%): ±0.05
Type: Neutral Density Filter
Parallelism (arcmin): <5
Clear Aperture (%): 90.00
Surface Accuracy: 2λ
Wavelength Range (nm): 700 - 1200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View