

Olympus LMPLFLN 20X Objective

See More by [Olympus](#)



Stock #88-204 3-4 DAYS

-

1

+

€2.238,00

ADD TO CART

Qty 1+
€2.238,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
26.00

Field of View (mm):
1.3

Focal Length FL (mm):
9.00

Model Number:

1-U2M345
Length excluding Threads (mm): 33.00
Magnification: 20X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.40
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.84
Depth of Field (µm): 1.72
Working Distance (mm): 12.0
Weight (g): 73
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--