

Olympus LMPLFLN-BD 10X Objective

See More by [Olympus](#)



#86-828

Stock **#86-828** [CONTACT US](#)

- 1 + **€1.951,00**

ADD TO CART

Qty 1+

€1.951,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
32.00

Field of View (mm):
2.65

Focal Length FL (mm):
18.00

Model Number: 1-U2N343
Length excluding Threads (mm): 35.00
Magnification: 10X
Maximum Diameter (mm): 32
Numerical Aperture NA: 0.25
Mounting Threads: M26 x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 1.34
Depth of Field (µm): 4.40
Working Distance (mm): 10.0
Weight (g): 84
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--