

Olympus MPLFLN 1.25X Objective

See More by [Olympus](#)



#16-880

Stock #16-880 3-4 DAYS

- 1 +

€3.222,00

ADD TO CART

Qty 1+

€3.222,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Diameter (mm):
28.00

Field of View (mm):
17.6

Focal Length FL (mm):
144.00

Model Number: 1-U2M920
Length excluding Threads (mm): 41.50
Magnification: 1.25X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.04
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): >70 from 400 - 700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 8.39
Depth of Field (µm): 171.88
Working Distance (mm): 3.5
Weight (g): 122
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 22
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--