

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



#86-814

Stock **#86-814** ☐ In Stock



1



€412,00

ADD TO CART

Qty 1+

€412,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
1.1

Focal Length FL (mm):
9.00

Model Number:
1-U2B225

Length excluding Threads (mm): 43.70
Magnification: 20X
Maximum Diameter (mm): 24
Numerical Aperture NA: 0.40
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.84
Depth of Field (µm): 1.72
Working Distance (mm): 1.2
Weight (g): 112.0
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 22
Parfocal Length (mm): 45
Immersion Liquid: N/A
Depth of Focus (µm): 688

Regulatory Compliance

RoHS 2015: Exempt
Reach 223: Contains SVHC(s)
Certificate of Conformance: View