

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

## Lumetica OQ LabScope 2.0 OCT Imaging System



OQ LabScope 2.0 OCT Imaging System

Stock #13-639 CLEARANCE CONTACT US

- 1 + €6.497,95

ADD TO CART

Qty 1+

€6.497,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Weight (lbs):  
6

Dimensions (mm):  
System: 413 x 216 x 153  
Scanner: 41 x 172 x 67

Model Number:  
OQ LabScope 2.0

Image Size (Pixels):  
512 x 512

|                                                      |
|------------------------------------------------------|
| <b>A-Scan Line Rate (lines/second):</b><br>13,000    |
| <b>B-Scan Image Rate (lines/second) :</b><br>20      |
| <b>Sensitivity (OSNR):</b><br>100 dB                 |
| <b>Depth Resolution (μm):</b><br>Air: 8<br>Tissue: 6 |
| <b>Transverse Resolution (μm):</b><br>18             |
| <b>Output Power (μW):</b><br>750                     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |