

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #20-255 3-4 DAYS



1



€7.089,00

ADD TO CART

Qty 1+

€7.089,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
10GigE

Type:
Color Camera

Manufacturer:

FLIR
Mounting Threads: Built-in 1/4-20 Tripod Mount Adapter
Image Buffer: 240MB
Camera Family: Oryx®
Model Number: ORX-10G-310S9C
Imaging Sensor: Sony IMX342
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: APS-C
Resolution (MegaPixels): 31.00
Pixels (H x V): 6,464 x 4,852
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 22.30 x 16.74
Frame Rate (fps): 26.00
Pixel Depth: 8/10/12 bit
Exposure Time: 39µs - 30s
Connector: GigE interface with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #19-803 Europe: #19-803 Japan: #19-803 Korea: Not Available China: #19-803
Power Consumption (W): 13.9
GPIOs: 1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 60 x 60 x 115
Weight (g): 508
Mount: F-Mount (With #20-256)
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 67.17
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

