

Pixelink M-Series M12BM-CYL Microscopy Monochrome Camera



Stock #17-810 3-4 DAYS

- 1 + **€2.895,00**

ADD TO CART

Qty 1+
€2.895,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Microscopy Camera

Manufacturer:
Pixelink

Mounting Threads:
No Mounting Threads/Tripod Adapter

Image Buffer:
Not Specified

Camera Family: M-Series
Model Number: M12BM-CYL
Imaging Sensor: Sony IMX304
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 12.30
Pixels (H x V): 4,096 x 3,000
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 14.1 x 10.4
Frame Rate (fps): 23.40
Pixel Depth: 8/12 bit
Exposure Time: Not Specified
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: None
Synchronization: Software Trigger
Dimensions (mm): 80.88 x 54.01 (excludes lens mount)
Weight (g): 218.5
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 70
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: None
Machine Vision Standard: USB3 Vision

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View