

Plastic Attachment Measuring Probe

See More by [Nikon](#)



Plastic Attachment Measuring Probe

Stock **#29-236** [CONTACT US](#)

-

1

+

€51^{,50}

ADD TO CART

Volume Pricing	
Qty 1+	€51,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Measurement Probe	Type:
Nikon	Manufacturer:

Regulatory Compliance	
View	Certificate of Conformance:

- 1µm Accuracy (at 20°C) and Measurement Length of 0 - 50mm
- 500mm/sec Maximum Response Speed
- Granite Platform Stand and 6 Measuring Probe Tips Available

Standard measurement attachment

M2.5x0.45

5

(14)

ø5

SR1.2

Plastic attachment

M2.5x0.45

14

ø5

4

9

ø3

SR1.5

Plastic

Flat attachment

M2.5x0.45

11

6

ø5

Pin attachment

M2.5x0.45

ø5

25

20

4

ø1.5

Roller attachment

ø8

3

M2.5x0.45

ø8

20

11

ø8

Flat attachment

M2.5x0.45

ø5

25

20

4

ø1.5

SR1.5

5±0.5

(17)

PID4485_Measurement_Probes