

[See all 53 Products in Family](#)

Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

See More by [IDS Imaging Development Systems](#)



#19-692: Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

Stock **#19-692** CLEARANCE **5 In Stock**

-

1

+

€214^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€214,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Camera Accessory	Type:
Note: 8-pin Binder Connector to open end, 2 branches: one branch 6 wires for Trigger and Flash (5m), one branch to Power Supply adapter (1.8m)	
Hardware & Interface Connectivity	
Length of Cable (m):	

5, 1.8	
8-pin Binder Connector	Connector:

Regulatory Compliance

View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.