

[See all 43 Products in Family](#)

Power Supply for 0.5-0.8mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock **#11-386** [CONTACT US](#)

-

1

+

€825⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€825,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Type:

Benchtop

Compatible Laser Models:

[1108](#), [1108P](#), [1107](#), [1107P](#)

Model Number:

SL92 Series

Compatible Laser Stock Number:
#62-714, #62-715, #62-716, #62-717

Features:
Turn Key, CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

9.00 x 5.50 x 2.38 Dimensions (inches):

Electrical

5 Output Power (W):
0.55/0.32 Input Current (A):

Hardware & Interface Connectivity

1250 Output Voltage (V):
4 Output Current (mA):
High Voltage Alden Connector Connector:
100/110/220 (AC) Input Voltage (V):

Regulatory Compliance

View Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

