

[See all 43 Products in Family](#)

Power Supply for 10mW HeNe Laser, AC, Bare Wire Leads (Recertified 05-P)



SL93 Series Power Supply (#11-381)

Stock **#11-381-RCD-05P** RECERTIFIED **1 In Stock**

⊖ 1 ⊕ €525⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€525,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

OEM Type:

[1135, 1135P](#) Compatible Laser Models:

SL93 Series Model Number:

[#62-726, #62-727](#) Compatible Laser Stock Number:

CDRH Delay (3-5 seconds)

Features:

Physical & Mechanical Properties

7.05 x 2.30 x 1.40 **Dimensions (inches):**

Electrical

20.15 **Output Power (W):**

0.75 (Max. Current Draw) **Input Current (A):**

Hardware & Interface Connectivity

3100 **Output Voltage (V):**

6.5 **Output Current (mA):**

High Voltage Alden Connector **Connector:**

100-250, 60/50Hz **Input Voltage (V):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

