

Power Supply for 1.5-2.0mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-385 3-4 DAYS

⊖ 1 ⊕

€331,00

ADD TO CART

Qty 1+

€331,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (inches):
4.00 x 1.50 x 1.00

Type:
OEM

Output Voltage (V):
1700

Output Current (mA):
4.9

Compatible Laser Models:

[1101](#), [1101P](#), [1103](#), [1103P](#)

Output Power (W):
8.33

Input Current (A):
1.36 (Max. Current Draw)

Connector:
High Voltage Alden Connector

Input Voltage (V):
24 DC

Model Number:
L28 Series

Compatible Laser Stock Number:
[#62-718](#), [#62-719](#), [#64-103](#), [#64-104](#)

Features:
CDRH Delay (3-5 seconds)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)