

Prism Mount



#53-030 + Cube Beamsplitter

Stock **#53-030** 20+ In Stock

-

1

+

€114⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€114,00 each
Qty 5-9	€102,60 each
Qty 10-49	€97,20 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fixed	Type:
Cube/Prism	Type of Optics:

Physical & Mechanical Properties	
Outer Diameter (inches):	


3.00	
	Outer Diameter (mm):
76.2	
Construction: Black Anodized Aluminum with Steel Post and Delrin Clamp	
Threading & Mounting	
	Size of Compatible Optics (mm):
50.0	
	Compatible Post:
1/4-20	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Reach 224:
Compliant	
	Certificate of Conformance:
View	

Product Details

- Easily Secure [Prisms](#) or [Cube Beamsplitters](#)
- Adjustable for Optics up to 55mm
- Rotary Version Offers Manual 360° Rotation

English Prism Mounts feature a steel post and anodized aluminum arm which eliminates obstructions in the optical path while still maintaining a secure position on the optic. Ideal for prisms and cube beamsplitters with a maximum height of 55mm, this prism mount features a V-cut clamp made of scratch resistant Delrin® to prevent damage to optics. The Prism Holder is also available as a complete assembly with the [Rotary Optic Mount](#), which allows smooth manual 360° rotation of the prism. English Prism Mounts have a locking knob that keep prisms securely positioned for increased repeatability.

Technical Information



53-030