

Red 300 x 300 Flat Dome Light



Effilux Flat Dome Lights

Stock #22-109 3-4 DAYS

- 1 + **€1.412,00**

ADD TO CART

Qty 1+
€1.412,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Red
Input Voltage (V): 24
Model Number: EFFI-FD-300-300-625
Dimensions (mm): 339 x 339 x 43.2

Wavelength (nm): 625.00
Weight (g): 3500
Power Consumption (W): 65
Power Supply: Power Supply Required and Sold Separately: USA: #15-874 Europe: #15-875 Japan: #15-876 Korea: Not Available China: #15-874
Active Area (mm): 300 x 300
Type of Illumination: LED Illuminator
Manufacturer: Effilux
Geometry: Flat Dome Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View