

Red Laser Pointer



Stock #52-840 **3 In Stock**

- 1 + €58⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€58,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Diode **Type of Laser:**

IIIa **Laser Class - CDRH:**

3.00 **Operating Lifetime (hours):**

Physical & Mechanical Properties

53.864 **Weight (g):**

0.5	Diameter (inches):
5.5	Length (inches):
Optical Properties	
650.00	Wavelength (nm):
Red	Color:
Electrical	
5 (Maximum)	Output Power (mW):
Hardware & Interface Connectivity	
1.5V, 2 AAA batteries (included)	Power Requirement:
Free Space	Output Type:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

Designed with the styling and power of our high-end models, this laser pointer offers lasting performance in a compact form. Measuring 5 1/2" L x 1/2" Dia., it features a brushed metal casing and delivers up to 3 hours of continuous use. Batteries included.

- 650nm Wavelength
- Handheld
- Battery Powered

Handheld laser pointers project visible targets up to 500 yards (1,500 ft.). A front-positioned push button ensures steady control during presentations, while the pen-sized design fits comfortably in your hand or pocket. Each pointer operates on two AAA batteries, built with sleek metal construction and a smooth finish. Please check product details for battery inclusion.