

## Rotary Mount



#52-572

Stock **#52-572** **20+ In Stock**

⊖ 1 ⊕ €178<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | €178,00 each                  |
| Qty 5+         | €160,20 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Rotary **Type:**

### Physical & Mechanical Properties

90°-0-90° with 1° increments **Scale Divisions:**

Black Anodized Aluminum **Construction:**

## Threading & Mounting

|                      |                  |
|----------------------|------------------|
| M42 x 0.75 (T-Mount) | Thread Type:     |
| 1/4-20               | Compatible Post: |

## Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

## Product Details

- Manual 360° Rotation
- Locking Thumb Screw for Secure Positioning and Alignment
- Compatible with [T-Mount Optic Mounts](#)

The Rotary Optic Mount allows smooth manual 360° rotation of optics for easy relative angular positioning. An ideal alternative for expensive rotary translation stages, this rotary optic mount can be used for aligning prisms, beam splitters, polarizers and other optical components using a 180° (90°-0-90°) scale with 1° increments. The mount is compatible with [T-Mount Optic Mounts](#). The Rotary Optic Mount is constructed of black anodized aluminum with a stainless-steel lever. [#52-573](#) includes a 4" long stainless steel mounting post [#59-000](#).

## Technical Information

