

TECHSPEC[®] Rugged Blue Series Kit IR/CUT, M12 Mount



C Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock **#73-075** [CONTACT US](#)

-

1

+

€1.820⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.820,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rugged Blue Series

Series:

C-Mount to M12 Adapter w/O-Ring, M12 Lens
Holder for Camera Boards, and 10 pack of M12 Lock
Nuts Included

Note:

Contents of Kit:

35-469
35-470
35-472
25-045
25-046
25-048
25-053
25-054
25-056
25-062
25-063
25-065
25-070
25-071
25-073
25-078
25-079
25-081
59-241
66-382
16-788

Included Focal Lengths or Magnifications:

2, 4, 6, 10, 16, 25

Optical Properties

Included F#:

2.5, 4, 8

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC [C](#), [UC](#), and [HP](#) Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [C Series](#): Compact (C), FA Lenses for Machine Vision
- [UC Series](#): Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- [HP Series](#): High Performance (HP), C-Mount Lenses for Machine Vision