

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



S-Mount Kinematic Mount (3-Screw Adjustment) (#11-133)

Stock #11-133 ■ In Stock



1



€123,00

ADD TO CART

Qty 1-49

€123,00

Qty 50+

€116,90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Mounting Threads:
M4

Thickness (mm):
19.60

Travel (mm):
Z-Axis: 6

Type: Tube Mount
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 7.0
Pointing Accuracy (μrad): 1.3
Adjustment Screw Pitch (mm): 0.20
Thread Type: S-Mount
Number of Adjustment Screws: 3
Aperture Size: M12 x0.5
Height (mm): 23.5
Function: Kinematic (Tip-Tilt)
Compatible Post: M4 x0.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View