

Schneider 60mm F-Mount Lens



Stock **#34-234** 1 In Stock

-

1

+

€2.169^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€2.169,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Schneider Large Format F-Mbunt VIS-NIR Lenses	Series:
Optimized Working Distance: 276mm - ∞	Note:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:

32.60	Length (mm):
49.0	Maximum Diameter (mm):
59.6	Outer Diameter (mm):
280.00	Weight (g):
8.9	Maximum Rear Protrusion (mm):

Optical Properties	
117 (35mm Sensor)	Field of View @ Min Working Distance (mm):
39.5°	Horizontal Field of View, 35mm Sensor:
60.00	Maximum Image Circle (mm):
60.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/4.0 - 4/16	Aperture (f/#):
<0.6	Distortion (%):
400 - 1000 BBAR	Coating:
VIS-NIR Color Corrected	Lens Wavelength Range:

Sensor	
60mm (Image Circle)	Maximum Sensor Format:
6.20	Pixel Size (µm):

Threading & Mounting	
M43.0 x0.75	Filter Thread:
F-Mount	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Full Frame, 35mm (Covers 46mm Image Circle), F-Mount Lens
- Color Corrected for Spectral Range of 400 – 1000nm
- 28mm to 100mm Focal Length

Ideal for surface inspection and line scan applications, Schneider Large Format F-Mount VIS-NIR Lenses offer low distortion and uniform performance across the entire focal plane. Featuring a lockable focus and iris, these lenses have been optically corrected for the 400 – 1000nm wavelength range. They can cover up to 35mm format sensors (43.3mm sensor diagonal). Schneider Large Format F-Mount VIS-NIR Lenses has been highly toleranced to eliminate tilt in the image plane, providing repeatable and accurate results.