

SCHOTT KG5, 12.5mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #18-503 3-4 DAYS

⊖ 1 ⊕ **€31,00**

ADD TO CART

Qty 1-10
€31,00

Qty 11+
€28,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Density (g/cm³):
2.53

Glass/Filter Number:

[SCHOTT KG5](#)

Substrate: ☐
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d :
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
565

Thickness (mm):
2.00 ±0.2

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d :
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Reach 223:
[Compliant](#)

Certificate of Conformance:
[View](#)