

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union ▼

SUBMIT



Stock #19-347 3-4 DAYS



1



€80,00

ADD TO CART

Qty 1-10

€80,00

Qty 11+

€70,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Density (g/cm³):
2.53

Glass/Filter Number:

SCHOTT KG5

Substrate: ☐
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d:
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
565

Thickness (mm):
1.00 ±0.1

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d:
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Reach 223:
[Compliant](#)

Certificate of Conformance:
[View](#)