

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



SCHOTT OG Glass (glass color will vary by product specification)



Stock **#16-930** ☒ In Stock



1



€263,00

ADD TO CART

Qty 1-10

€263,00

Qty 11+

€236,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Dimensions (mm):**  
165.0 x 165.0 +3.0/-0.0

**Density (g/cm³):**  
2.56

|                                                                  |
|------------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">SCHOTT OG590</a></div> |
| <div>Length (mm):<br/>165.00</div>                               |
| <div>Coating:<br/>Uncoated</div>                                 |
| <div>Color:<br/>Red</div>                                        |
| <div>Index of Refraction <math>n_d</math>:<br/>1.51</div>        |
| <div>Transformation Temperature (°C):<br/>506</div>              |
| <div>Thickness (mm):<br/>4.50 ±0.5</div>                         |
| <div>Type:<br/>Longpass Filter</div>                             |
| <div>Wavelength:<br/>VIS</div>                                   |
| <div>Width (mm):<br/>165.00</div>                                |
| <div>Edges:<br/>Break Edges</div>                                |
| <div>Reflection Factor <math>P_d</math>:<br/>0.92</div>          |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
|-----------------------------------------------------------------|