

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

SCHOTT RG850, 12.5mm Dia., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-455 ☐ In Stock



1



€32,00

ADD TO CART

Qty 1-10

€32,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
850.00 ±9

Density (g/cm³): 2.93
Glass/Filter Number: SCHOTT RG850
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 1200
Passband Limit 2 λ_{p2} (nm): 1200
Index of Refraction n_d: 1.56
Spectral Transmittance t_p (%): 97
Stopband Limit λ_s(nm): 700
Surface Quality: 60-40
Transformation Temperature (°C): 554
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--