



# SCHOTT UG11, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-372** 3-4 DAYS

[Additional Bandwidths](#)

- 1 + **€47,00**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| €47,00   |

|         |
|---------|
| Qty 11+ |
| €41,00  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**ⓘ** Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Diameter (mm):**  
12.50

**Center Wavelength CWL (nm):**  
325.00

|                                                            |
|------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.92                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT UG11</a> |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Black                                     |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.56          |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>545             |
| <b>Thickness (mm):</b><br>2.00 ±0.2                        |
| <b>Type:</b><br>Bandpass Filter                            |
| <b>Wavelength:</b><br>UV                                   |
| <b>Bevel:</b><br>Protective as needed                      |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|