



SCHOTT VG9, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-401** ☐ In Stock

[Additional Bandwidths](#)

1 **€41,00**

ADD TO CART

Qty 1-10
€41,00
Qty 11+
€37,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
525.00

Density (g/cm³): 2.87
Glass/Filter Number: SCHOTT VG9
Coating: Uncoated
Color: Green
Index of Refraction n _d : 1.55
Surface Quality: 60-40
Transformation Temperature (°C): 462
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
