

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT



SCHOTT VG Glass (glass color will vary by product specification)

Stock #16-945 3-4 DAYS



1



€505,00

ADD TO CART

Qty 1-10

€505,00

Qty 11+

€453,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.87

Glass/Filter Number:
[SCHOTT VG9](#)

Length (mm): 165.00
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Transformation Temperature (°C): 462
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--