

## Sectional LED Ring Light, 220V



Stock #68-770 **1 In Stock**

⊖ 1 ⊕ €260<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	€260,00 each
Qty 6+	€234,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

72.00 **Number of LEDs:**

LED Illuminator **Type of Illumination:**

**Note:**  
Power Supply Included  
Requires 110V to 220V Inversion for Use in the US

Ring Light **Geometry:**

---

Constant

**Illumination Mode:**

## Physical & Mechanical Properties

60.5

**Inner Diameter (mm):**

## Optical Properties

White

**Color:**

## Hardware & Interface Connectivity

220.00

**Operating Voltage (V):**

## Environmental & Durability Factors

6400.00

**Color Temperature (K):**

## Regulatory Compliance

[View](#)

**Certificate of Conformance:**

---

## Product Details

- Large Inner Diameters for Easy Mounting
- 6400K Color Temperature
- Features Sectional Light Control

LED Ring Light Illuminators are strong alternatives to traditional fluorescent ring lights. The sectional ring light features lighting control in each of the unit's four quadrants, a 60.5mm inner diameter, and 72 LEDs. The sectional ring light is controlled using a panel on the top of the unit. LED Ring Light Illuminators are ideal for use with reflective parts and features a 70mm inner diameter and 60 LED bulbs. Sectional Light Control and Polarizer/Analyzer models are available.

Note: Due to CE restrictions, [#68-771](#) Polarizer/Analyzer LED Ring Light is not available in all regions. Please [contact us](#) for a suitable replacement.

---