

Small X-Axis Leadscrew Drive



Stock **#36-035** 20+ In Stock

-

1

+

€241^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	€241,00 each
Qty 10+	€212,40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Metric

Physical & Mechanical Properties

Type of Movement:

Linear (X)	
	Guide System:
Dovetail	
	Stage Size (mm):
24 x 30	
	Travel (mm):
10 (±5)	
	Center Hole:
5.8mm Thru	
	Construction:
Brass	
	Leadscrew Pitch (mm):
0.5	
	Load Capacity (kg):
3.5	
	Weight (kg):
0.11	

Hardware & Interface Connectivity

	Type of Drive:
Lead Screw	

Threading & Mounting

	Mounting Threads:
(6) M3 x 0.5	

Regulatory Compliance

	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	Reach 247:
Contains SVHC(s)	

Product Details

- Locking Knobs for Secure Positioning
 - 0.5mm Travel per Knob Rotation
 - Available with up to 15mm Travel in X and Y with 12mm Travel in Z
- Leadscrew Drive Stages are ideal for a variety of positioning requirements that require high load capacities. Each stage features a leadscrew drive and locking knobs for securing the stage position. A top plate is available for large models ([#58-290](#)) with both M6 and 1/4-20 tapped holes to directly accept posts or post holders. Large models feature an aluminum base plate for easy integration.

Technical Information

