

Small X-Y-Z Axis Leadscrew Drive Stage



X-Y Axis Leadscrew Drive Metric Stages



Stock #36-037 **15 In Stock**

⊖ 1 ⊕ €715⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | €715,00 each |
| Qty 10+ | €633,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**

Physical & Mechanical Properties

Linear (X-Y-Z) **Type of Movement:**

| | |
|------------|------------------------------|
| Dovetail | Guide System: |
| 24 x 30 | Stage Size (mm): |
| 10 (±5) | Travel (mm): |
| 5.8mm Thru | Center Hole: |
| Brass | Construction: |
| 0.5 | Leadscrew Pitch (mm): |
| 1.2 | Load Capacity (kg): |
| 0.34 | Weight (kg): |

Hardware & Interface Connectivity

| | |
|------------|-----------------------|
| Lead Screw | Type of Drive: |
|------------|-----------------------|

Threading & Mounting

| | |
|--------------|--------------------------|
| (6) M3 x 0.5 | Mounting Threads: |
|--------------|--------------------------|

Regulatory Compliance

| | |
|----------------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |
| Contains SVHC(s) | Reach 247: |

Product Details

- Locking Knobs for Secure Positioning
- 0.5mm Travel per Knob Rotation
- Available with up to 15mm Travel in X and Y with 12mm Travel in Z

Leadscrew Drive Stages are ideal for a variety of positioning requirements that require high load capacities. Each stage features a leadscrew drive and locking knobs for securing the stage position. A top plate is available for large models ([#58-290](#)) with both M6 and 1/4-20 tapped holes to directly accept posts or post holders. Large models feature an aluminum base plate for easy integration.

Technical Information

