

[See all 16 Products in Family](#)

SWIR 1200nm Homogeneous Backlight



Efflux SWIR LED Backlights

Stock **#28-629** **2 In Stock**

⊖ 1 ⊕ €2.390⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€2.390,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

EFFI-MBL-100T-100-1200 **Model Number:**

LED Illuminator **Type of Illumination:**

>90% **Uniformity (%):**

Efflux **Manufacturer:**

Backlight

Geometry:

Illumination Mode:

Continuous with AIC (Analog Intensity Control)

Physical & Mechanical Properties

Dimensions (mm):

136.5 x 109.5 x 80.0

Active Area (mm):

100 x 100

Optical Properties

Color:

SWIR

Wavelength (nm):

1,200

Hardware & Interface Connectivity

Connector:

M12, 4 pins

Input Voltage (V):

24VDC

Power Supply:

Power Supply Required and Sold Separately.

USA: [#15-874](#)

Europe: [#15-875](#)

Japan: [#73-409](#)

Korea: [#73-409](#)

China: [#15-874](#)

Environmental & Durability Factors

Operating Temperature (°C):

-20 to 70

Environmental Rating:

IP50

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Feature >80% Homogeneity at Design Wavelength

Effilux SWIR LED Backlights provide intense and uniform lighting for machine vision, sorting and silicon inspection applications. These are available in wavelengths of 1050, 1200, 1300, 1450, 1550, and 1650nm. The backlights are designed with >80% homogeneity at their design wavelengths. Effilux SWIR LED Backlights are ideal complements for applications utilizing TECHSPEC® C Series Fixed Focal Length SWIR Lenses, TECHSPEC® SilverTL™ SWIR Telecentric Lenses and LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) SWIR Cameras or Teledyne FLIR IIS Forge 1GigE SWIR Cameras.