

## TECHSPEC® T-Mount Aperture Cap



#66-037: T-Mount Aperture Cap

Stock **#66-037** **20+ In Stock**

⊖ 1 ⊕ €31<sup>75</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€31,75 each
Qty 5-9	€28,40 each
Qty 10-25	€26,70 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Tube Cap **Function:**

#### Physical & Mechanical Properties

5.0 **Total Length (mm):**

**Thickness (mm):**

4.00

Extension Length (mm):

54.5

## Threading & Mounting

Thread Type:

T-Mount

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

## Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

**Note:** #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

## Technical Information

