

[See all 13 Products in Family](#)

TECHSPEC® T-Mount, 40mm Cube Mount, 1/4-20



12.5mm x 17.5mm Plate S-Mount Holder



Stock #63-981 **1 In Stock**

⊖ 1 ⊕ €484.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€484,00 each
Qty 5-9	€427,30 each
Qty 10-25	€393,40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Cube

Note:
Includes four T-Mount Aperture Caps ([#66-037](#))

Dimensions of Compatible Optics (mm):
40.0 Sq.

Physical & Mechanical Properties

Dimensions (mm):
54.5 x 54.5 x 63.8

Extension Length (mm):
54.5

Min. Thickness of Compatible Optics (mm):
40.0

Max. Thickness of Compatible Optics (mm):
40.0

Threading & Mounting

Thread Type:
T-Mount

Compatible Post:
1/4-20

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

